


Replacement Parts List

Leopard Series Short Chambered Systems



LeopardUV® Model Numbers:


High Output—LP1SHO-6, LP2SHO-6, LP3SHO-6, LP3SHO-8, LP4SHO-6, LP4SHO-8

Amalgam—LP1SA-6, LP2SA-6, LP3SA-6, LP3SA-8, LP4SA-6, LP4SA-8, LP5SA-8, LP6SA-8, LP8SA-8

Item No.	Part No.	Description	Quantity Required # Of Lamps in system						
			1 Lamp	2 Lamp	3 Lamp	4 Lamp	5 Lamp	6 Lamp	8 Lamp
1	LH0001 LH0002	Lamp Harness (4 wire) Lamp Harness (2 wire)	1	2	3	4	5	6	8
2	CN0005	Compression Cap with hole for Lamp Harness	1	2	3	4	5	6	8
3	CN0004 CN0006	Compression Nut	2	4	6	8	10	12	16
		Compression Cap (not shown)	1	2	3	4	5	6	8
4	SS1015 2-0159	Sleeve Washer, Stainless Steel Sleeve Washer, Stainless Steel (For Wiper System)	2	4	6	8	10	12	16
5	ORNG0102 AQ35492	Sleeve, O-Ring, EPDM Sleeve O-Ring, EPDM (For Wiper System)	2	4	6	8	10	12	16
6	GL-5843-4H74Y	UV Lamp—High Output 254NM	1	2	3	4	5	6	8
	GV-5843-4H74A	UV Lamp—High Output 185NM							
	GL-6843-4A74G	UV Lamp—Amalgam 254NM							
	GV-6843-4A74B	UV Lamp—Amalgam 185NM							
7	QZ53-968 QZ47-962	Quartz Sleeve, Open Quartz Sleeve, Open (For Wiper System)	1	2	3	4	5	6	8
8	GSKT0014	Head Gasket—for 6” Chambers	2						
	GSKT0004	Head Gasket—for 8” Chambers							
Model Options									
9	VPM0001 002045	UV Viewport O-Ring for Viewport (Models without UV Monitoring System)	1						
10	4-0008	UV Sensor Probe	1						
	ORNG0101	O-Ring for Sensor Probe (Models with Standard UV Meter Board)							
	SNSR0004	UV Sensor Probe							
	ORNG0101	O-Ring for UV Sensor Probe							
	SNSR0005	UV Sensor Probe							
	SW0001	Sight Window for Sensor Probe							
ORNG0102	O-Ring for Sight Window (Models with WatchDog Monitoring System)								
11	THERM0100	Thermistor (Models with Standard High Heat)	1						

Replacement Parts List

Leopard Series Long Chambered Systems



LeopardUV® Model Numbers:


High Output—LP4LHO-6, LP4LHO-8, LP5LHO-6, LP5LHO-8, LP6LHO-8

Amalgam—LP4LA-8, LP5LA-8, LP6LA-8, LP4LA-10, LP5LA-10

Item No.	Part No.	Description	Quantity Required # Of Lamps in system		
			4 Lamp	5 Lamp	6 Lamp
1	LH0002	Lamp Harness (2 wire)	4	5	6
2	CN0005	Compression Cap with hole for Lamp Harness	4	5	6
3	CN0004	Compression Nut	8	10	12
4	SS1015 2-0159	Sleeve Washer, Stainless Steel Sleeve Washer, Stainless Steel (For Wiper System)	8	10	12
5	ORNG0102 AQ35492	Sleeve O-Ring, EPDM Sleeve O-Ring, EPDM (For Wiper System)	8	10	12
6	GL-51554-4H74Y GV-51554-4H74A GL-61570-4A74G GV-61570-4A74B	UV Lamp—High Output 254NM UV Lamp—High Output 185NM UV Lamp—Amalgam 254NM UV Lamp—Amalgam 185NM	4	5	6
7	QZ53-1643 QZ47-1637	Quartz Sleeve, Open Quartz Sleeve, Open (For Wiper System)	4	5	6
8	GSKT0014 GSKT0004 GSTK0005	Head Gasket (For 6" Chamber) Head Gasket (For 8" Chamber) Head Gasket (For 10" Chamber)	2 2 2	2 2 2	X 2 X
Model Options					
9	VPM0001 002045	UV Viewport O-Ring for UV Viewport (Models without UV Monitoring System)	1		
10	4-0008 ORNG0101 SNSR0004 ORNG0101 SNSR0005 SW0001 ORNG0102	UV Sensor O-Ring for sensor probe (Models with Standard UV Meter Board) UV Sensor Probe O-Ring for UV Sensor Probe UV Sensor Probe Sight Window for Sensor Probe O-Ring for Sight Window (Models with WatchDog Monitoring System)	1		
11	THERM0100	Thermistor (Models with Standard High Heat)	1		
12	CN0006	Compression Cap	4	5	6

Replacement Parts List

Leopard Series Electrical Enclosure



****WatchDog and Standard Monitoring System is not included in parts blowup****

LeopardUV® Model Numbers:**High Output Models****Short—LP1SHO-6, LP2SHO-6, LP3SHO-6, LP3SHO-8, LP4SHO-6, LP4SHO-8****Long—LP4LHO-6, LP4LHO-8, LP5LHO-6, LP5LHO-8, LP6LHO-8****Amalgam Models****Short—LP1SA-6, LP2SA-6, LP3SA-6, LP3SA-8, LP4SA-6, LP4SA-8, LP5SA-8, LP6SA-8, LP8SA-8****Long—LP4LA-8, LP5LA-8, LP6LA-8, LP4LA-10, LP5LA-10**

Item No.	Part No.	Description	Quantity Required # Of Lamps in system						
			1 Lamp	2 Lamp	3 Lamp	4 Lamp	5 Lamp	6 Lamp	8 Lamp
1	ELEN0028	Intensity Display Board (Models with Standard UV Meter Board Option)	1	1	1	1	1	1	1
2	LED0100-29	Lamp Status Indicator	1	2	3	4	5	6	8
3	ERTM0100	Elapsed Runtime Meter	1	1	1	1	1	1	1
4	LGHT0003	Low UV Indicator—120V	1	1	1	1	1	1	1
	LGHT0004	Low UV Indicator—220V (Models with Standard UV Meter Board Option)	1	1	1	1	1	1	1
5	LGHT0001	High Heat Shutoff Indicator—120V	1	1	1	1	1	1	1
	LGHT0002	High Heat Shutoff Indicator—220V (Models with Standard High Heat Option)	1	1	1	1	1	1	1
6	ELEN0029-420	UV Meter Board with 4-20mA Output (Models with Standard UV Meter Board Option)	1	1	1	1	1	1	1
7	BLST0034	Ballast 100-277V 50-60Hz (Short High Output Lamp)	1	2	3	4	X	X	X
	BLST0056	Ballast 120-240V 50-60Hz (Short HO Lamp Out Alert)	1	2	3	4	X	X	X
	BLST0066	Ballast 120-277V 50-60Hz (Long High Output Lamp)	X	X	X	2	3	3	X
	BLST0058	Ballast 220-277V 50-60Hz (Long HO Lamp Out Alert)	X	X	X	2	3	3	4
	BLST0015	Ballast 120V 50-60Hz (Short Amalgam Lamp)	1	2	3	4	5	6	8
	BLST0016	Ballast 220V 50-60Hz (Short Amalgam Lamp)	1	2	3	4	5	6	8
	BLST0057	Ballast 220-277V 50-60Hz (Short Amalgam Lamp Out Alert)	1	2	3	4	5	6	8
	BLST0003	Ballast 120V 50-60Hz (Long Amalgam Lamp)	X	X	X	4	5	6	X
	BLST0004	Ballast 230V 50-60Hz (Long Amalgam Lamp)	X	X	X	4	5	6	X
	BLSTA0073-01	Ballast 220V 50Hz (Long Amalgam Lamp Out Alert)	X	X	X	2	3	3	X